

S.No.	Brand	Design	Index	Material	Tint	Fitting Height	Engraving Nasal Side	Engraving Temporal Side	Fitting Cross
1	Nova HD	Regular	1.74	Plastic	Clear/Tinted	19 mm	1.74 ○ 5	N HD ○ 2.00	3mm above geometric centre
2	Nova HD	Regular	1.74	Transtions VI	Gray/Brown	19 mm	1.74 ○ TVI 5	N HD ○ 2.00	3mm above geometric centre
3	Nova HD	Regular	1.67	Plastic	Clear/Tinted	19 mm	1.67 ○ 5	N HD ○ 2.00	3mm above geometric centre
4	Nova HD	Regular	1.67	Transtions VI	Gray/Brown	19 mm	1.67 ○ TVI 5	N HD ○ 2.00	3mm above geometric centre
5	Nova HD	Regular	1.67	Transitions Xtractive	Gray	19 mm	1.67 ○ XA 5	N HD ○ 2.00	3mm above geometric centre
6	Nova HD	Regular	1.67	Polarised	Gray/Brown	19 mm	1.67 ○ POL 5	N HD ○ 2.00	3mm above geometric centre
7	Nova HD	Regular	1.60	Plastic	Clear/Tinted	19 mm	1.60 ○ 5	N HD ○ 2.00	3mm above geometric centre
8	Nova HD	Regular	1.60	Transtions VI	Gray/Brown	19 mm	1.60 ○ TVI 5	N HD ○ 2.00	3mm above geometric centre
9	Nova HD	Regular	1.60	Transitions Xtractive	Gray	19 mm	1.60 ○ XA 5	N HD ○ 2.00	3mm above geometric centre
10	Nova HD	Regular	1.60	Polarised	Gray/Brown	19 mm	1.60 ○ POL 5	N HD ○ 2.00	3mm above geometric centre
11	Nova HD	Regular	1.59	Polycarbonate	Clear/Tinted	19 mm	1.59 ○ 5	N HD ○ 2.00	3mm above geometric centre
12	Nova HD	Regular	1.59	Polycarbonate Transitions VI	Gray/Brown	19 mm	1.59 ○ PC T-VI 5	N HD ○ 2.00	3mm above geometric centre
13	Nova HD	Regular	1.59	Poly Transitions Xtractive	Gray	19 mm	1.59 ○ XA 5	N HD ○ 2.00	3mm above geometric centre

S.No.	Brand	Design	Index	Material	Tint	Fitting Height	Engraving Nasal Side	Engraving Temporal Side	Fitting Cross
14	Nova HD	Regular	1.59	Polycarbonate Polarised	Gray / Brown / G-15 / Copper	19 mm	1.59 ○ PC POL 5	N HD ○ 2.00	3mm above geometric centre
15	Nova HD	Regular	1.59	Polycarbonate Drivewear	Brown	19 mm	1.59 ○ DW 5	N HD ○ 2.00	3mm above geometric centre
16	Nova HD	Regular	1.57	Plastic	Clear/Tinted	19 mm	1.56 ○ FX 5	N HD ○ 2.00	3mm above geometric centre
17	Nova HD	Regular	1.56	Plastic	Clear	19 mm	1.56 ○ 5	N HD ○ 2.00	3mm above geometric centre
18	Nova HD	Regular	1.53	Trivex	Clear/Tinted	19 mm	1.53 ○ TRL 5	N HD ○ 2.00	3mm above geometric centre
19	Nova HD	Regular	1.53	Trivex Transitions VI	Gray/Brown	19 mm	1.53 ○ TRI TVI 5	N HD ○ 2.00	3mm above geometric centre
20	Nova HD	Regular	1.53	Trivex Transitions Xtractive	Gray	19 mm	1.53 ○ XA 5	N HD ○ 2.00	3mm above geometric centre
21	Nova HD	Regular	1.53	Trivex Polarised	Gray/Brown	19 mm	1.53 ○ TRI POL 5	N HD ○ 2.00	3mm above geometric centre
22	Nova HD	Regular	1.50	Plastic	Clear/Tinted	19 mm	1.50 ○ 5	N HD ○ 2.00	3mm above geometric centre
23	Nova HD	Regular	1.50	Transtions VI	Gray/Brown	19 mm	1.50 ○ TVI 5	N HD ○ 2.00	3mm above geometric centre
24	Nova HD	Regular	1.50	Transitions Xtractive	Gray	19 mm	1.53 ○ XA 5	N HD ○ 2.00	3mm above geometric centre
25	Nova HD	Regular	1.50	Polarised	Gray / Brown/G-15/ Copper	19 mm	1.50 ○ POL 5	N HD ○ 2.00	3mm above geometric centre
26	Nova HD	Regular	1.50	Drivewear Transitions	Brown	19 mm	1.50 ○ DW 5	N HD ○ 2.00	3mm above geometric centre

DESIGNS

Regular		Denoted by 5
Short		Denoted by 3
Xtra Short		Denoted by only Nova
Super Short		Denoted by only Nova